



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln
79109-3210, TX Amarillo
Phone: 806-220-0404
Fax: 806-220-0811



C4 #4 Cu Long Barrel Compression Butt Splice

Nsi Industries

Catalog Number	C4
Manufacturer	Nsi Industries
Description	Compression Splice Connector, #6 Awg Conductor Size, #4 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Gray Insulation Color, 2 Conductors, +90 °C Operating Temperature, 1.752 In Overall Length, Compression Terminal, 600 V, 0.052 LB/Ea
Weight per unit	0.0520 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Gray
Finish	Tin Plated

Dimensions and Weight

Size	L=1.75 - OD=.340 - ID=.250
------	----------------------------

Descriptions

Description	#4 CU LONG BARREL COMPRESSION BUTT SPLICE
extra long description	NSI C-4 Tinned Copper Splice- Long
Features	Long Barrel TinnedCopperSplice4 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

Manufacturer Information

GTIN	00662381037510
UPC	662381037510

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Long Barrel - CU Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln
79109-3210, TX Amarillo
Phone: 806-220-0404
Fax: 806-220-0811

Packaging

Carton	1
Package	100
Weight Per each	0.052

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)
Temperature Rating	90 C