

# Eaton C440A2A020SAX

Catalog Number: C440A2A020SAX

Eaton C440 electronic overload relay, C440 Electronic Overload Relay - NEMA, Separate Mount, 45mm frame, Selectable 10A, Class 10 ,20, 30, Overload 4-20A, Ground fault sensing

## General specifications



### Product Name

Eaton C440 electronic overload relay

### Catalog Number

C440A2A020SAX

### UPC

786685412405

### Product Length/Depth

4.32 in

### Product Height

6.5 in

### Product Width

1.8 in

### Product Weight

0.87 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CE Marked

### Certifications

CSA Certified  
UL Listed

## defaultTaxonomyAttributeLabel

### Overload range

4-20A

### Special features

Ground fault sensing

### Type

Electronic overload relay

### Frame size

45 mm

### Rated short-time withstand current (Icw)

Auto

Manual

### Trip type

Selectable 10 A, class 10 ,20, 30

### Size

Separate Mount

## Resources

### Brochures

C440 Electronic Overload Relay

### Catalogs

Eaton's Volume 5—Motor Control and Protection

### Drawings

C440A\_AX AutoCAD 2D Footprint

C440A\_AX 3D Inventor

C440A\_AX 2D PDF

C440A\_AX 3D Model Xchange

C440A\_AX 2D Drawing Xchange

C440A\_AX AutoCAD 2D Footprint (mm)

### Installation instructions

C440 NEMA Electronic Overload - Self Powered

### Specifications and datasheets

Eaton Specification Sheet - C440A2A020SAX

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia