



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1617 W Highway 30
70737-0000, LA Gonzales
Phone: 225-960-6273
Fax: 225-960-6274



C502H 2 HR Twist Timer With Metal Wallplate

Nsi Industries

Catalog Number	C502H
Manufacturer	Nsi Industries
Description	Twist Timer, 2 H Time Setting Mode, SPDT Contact Form, 2 H Time Setting, 125 to 277 V, 1 Pole, White, +32 °F Operating Temperature, +122 °F Operating Temperature, 3 X 5 In Size, 0.4 LB
Weight per unit	0.4000 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Wall Plate
Contact Rating	125-250-277 VAC
Phase	Single Phase
Poles	1
Timing Range	2 Hour

Descriptions

Description	2 HR TWIST TIMER WITH METAL WALLPLATE
extra long description	TORK C502H 2 Hour Spring Wound Twis

Manufacturer Information

GTIN	00786261155078
Manufacturers Part Number	C502H
UPC	786261155078

Taxonomies, Classifications, and Categories

Category Description	1PH MANUAL STARTERS
Type	Spring Wound In Wall Time Switch-Commercial Grade

Packaging

Carton	1
Weight Per each	0.4

Uses, Certifications, and Standards

Enclosure	Single Gang Wall Plate
environmental conditions	32-122 F
Frequency Rating	50-60 Hz
Mounting	Single Gang Wall Plate
Operating Temperature	32-122 F
standard	cULus