

Specifications



Photo is representative

Eaton CCP1044CD

Eaton Crouse-Hinds series PowerMate CCP plug, 100A, 0.875-1.906", Four-wire, four-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CCP plug
CATALOG NUMBER	CCP1044CD
UPC	662276276666
PRODUCT LENGTH/DEPTH	10.8 in
PRODUCT HEIGHT	4.13 in
PRODUCT WIDTH	4.13 in
PRODUCT WEIGHT	2.2 lb
PRODUCT TYPE	Plug

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Product specifications

AMPERAGE RATING	100A
GROUNDING TYPE	Style 1
CONFIGURATION	Four-wire, four-pole
CABLE DIAMETER	0.875-1.906"
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum

Resources

3D CAD DRAWING PACKAGE	Eaton Crouse-Hinds CCP1044CD 3D drawing
BROCHURES	PowerMate Drilling Pin and Sleeve Devices brochure
CATALOGS	PowerMate Drilling Pin and Sleeve Devices catalog page
CERTIFICATION REPORTS	PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors) PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)
INSTALLATION INSTRUCTIONS	IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing
SPECIFICATIONS AND DATASHEETS	PowerMate Connectors Eaton Specification Sheet - CCP1044CD

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

