

# Eaton CCV2150

Catalog Number: CCV2150

Eaton Type CCV Tenant Main Circuit Breaker, Tenant main circuit breaker, 150 A, 10 kAIC, Two-pole, 120/240 V, #2/0 AWG-300 kcmil Cu/Al, CCV, Type ECC unit enclosures

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CCV tenant main breaker	CCV2150
<b>UPC</b>	<b>Product Length/Depth</b>
786685368450	7.7 in
<b>Product Height</b>	<b>Product Width</b>
5.4 in	4.5 in
<b>Product Weight</b>	<b>Warranty</b>
2.9 lb	Limited lifetime residential, 1 year commercial
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.

## Type

Tenant main circuit breaker

## Amperage Rating

150 A

## Voltage rating

120/240 V

## Circuit breaker frame type

CCV

## Used with

Type ECC Unit Enclosures

## Interrupt rating

10 kAIC

## Main circuit breaker

CCV

## Wire size

#2/0 AWG-300 kcmil Cu/Al

## Number of poles

Two-pole

## Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

## Specifications and datasheets

[Eaton Specification Sheet - CCV2150](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)