

# COMMERCIAL DIMMERS & FAN SPEED CONTROLS

## Titan® Series Dimmers & Fan Speed Controls



**A complete solution for easy, economical multi-gang installations.**

The Wattstopper Titan® Series dimmers have key features designed to increase installer productivity. Each comes with all the screwless wall plate components necessary for single gang or multi-gang installations. No need to order any additional components such as long-lead time custom wall plates to finish the job. Complete the installation with everything right out of the box, increasing productivity by finishing up in one visit instead of several.

### CD703PW

#### Titan Commercial Dimmers

- A. Exclusive labeling system has a built-in label holder** enabling instant circuit identification; looks clean and professional.
- B. Included end-caps and spacers** screw directly to heat sinks; center plate snaps easily on and off.
- C. Enclosed slider** helps prevent dust and dirt contamination.
- D. Exclusive adjustable limit control in incandescent dimmers saves energy** and extends bulb life — reduces maximum output by up to 10 percent.
- E. Air-gap switch**
- F. Improved heat management** enables superior load ratings.


**Included screwless wall plate components** make it easy to assemble a custom multi-gang wall plate in any configuration — saving money and time.

**Preset models** feature large ON/OFF button and single pole/three-way functionality.

**High-reliability design with** built-in surge and static protection plus oversize output devices to stand up to abuse.

**Power-failure memory** retains presets through power outages.

**Widest choice of amperage ratings** with minimal or no de-rating for faster job planning.



**CDADAPTORKITW**






**Adaptor kit enables matching installation of standard P&S Decorator-Style Devices** – outlets, switches, GFCIs and more. See page 0-21 for ordering information.



# COMMERCIAL DIMMERS & FAN SPEED CONTROLS

## Titan® Series Incandescent Dimmers


**CD703PW - Narrow**

**CD1100W - Narrow**

**CD1603PW - Wide**

**CD2003PW - Wide**

CATALOG NUMBER	DESCRIPTION	RATINGS	NARROW OR WIDE	COLOR
<b>INCANDESCENT</b>				
CD700I CD700W CD700 CD700GRY CD700BK CD700LA	Single Pole, Slide-to-OFF	120V, 700W	Narrow	Ivory White Brown Gray Black Light Almond
CD703PI CD703PW CD703P CD703PGRY CD703PBK CD703PLA	Single Pole/3-Way, Preset	120V, 700W	Narrow	Ivory White Brown Gray Black Light Almond
CD1100I CD1100W CD1100 CD1100GRY CD1100BK CD1100LA	Single Pole, Slide-to-OFF	120V, 1100W	Narrow	Ivory White Brown Gray Black Light Almond
CD1103PI CD1103PW CD1103P CD1103PGRY CD1103PBK CD1103PLA	Single Pole/3-Way, Preset	120V, 1100W	Narrow	Ivory White Brown Gray Black Light Almond
CD1600I CD1600W CD1600 CD1600GRY CD1600BK CD1600LA	Single Pole, Slide-to-OFF	120V, 1600W	Wide	Ivory White Brown Gray Black Light Almond
CD1603PI CD1603PW CD1603P CD1603PGRY CD1603PBK CD1603PLA	Single Pole/3-Way, Preset	120V, 1600W	Wide	Ivory White Brown Gray Black Light Almond
CD2000I CD2000W CD2000 CD2000GRY CD2000BK CD2000LA	Single Pole, Slide-to-OFF	120V, 2000W	Wide	Ivory White Brown Gray Black Light Almond
CD2003PI CD2003PW CD2003P CD2003PGRY CD2003PBK CD2003PLA	Single Pole/3-Way, Preset	120V, 2000W	Wide	Ivory White Brown Gray Black Light Almond

### Features

- Field configurable wall plate system.
- Labeling system.
- Adjustable top end output voltage.
- Shipped with protective film.
- Rugged construction.
- Superior ratings with a minimum of de-rating when ganged.
- Simple to plan the rough-in.
- Available in single pole slide-to-OFF and single pole/3-way preset models.
- Attractive European styling.
- Eye-catching packaging.
- Exclusive adaptor kit to install other decorator-style opening devices under the Titan® wall plate system. (See Page O-21.)
- Blank center plate included.

For technical specifications, de-rating, and rough-in box charts, see U-170.

All devices listed on this page conform to NEMA WD-1 and WD-6. UL Listed and CSA Certified.