



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.  
75119-0000, TX Ennis  
Phone: 972-875-3413  
Fax: 972-875-3174



## CE120FU15M5 120V Extender *Lithonia Lighting - Acuity*

Catalog Number	CE120FU15M5
Manufacturer	Lithonia Lighting - Acuity
Description	Cable Extender, 120V, 12AWG, 4 Conductor and 1 Ground, 15 Feet, Sku - 710577
Weight per unit	5.0 (lbs/each)
Product Category	Portable Cord Sets

### Features

Hardware	Yes
Lamp Included	NO
Lamp Type	Not Applicable
lumens	Lamp Not Included
Material	Aluminum
pallet quantity	135
Voltage Rating	120
Warranty	5

### Material, Color, and Finish

Color	Silver
Finish	Unfinished
Lens Material	Not Applicable

### Descriptions

Description	120V EXTENDER
extra long description	LITH CE 120 F U 15 M5 Cable Extende
Long Description	Cable Extender, 120V, 12AWG, 4 Conductor and 1 Ground, 15 feet, SKU - 710577
Product Type	Modular Wiring
Special Features	Holoflex is a modular wiring system designed to address the high labor cost and fast pace of today's construction projects, weather it is new or existing construction, Holoflex reduces the installation time associated with hardwire systems by as much as 75%. This translates directly to quicker installation and labor cost savings, which help keep your project on time and within budget. Used in Manufacturing, Retail, Automotive, Recreational Buildings, Warehousing.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.  
75119-0000, TX Ennis  
Phone: 972-875-3413  
Fax: 972-875-3174

## Manufacturer Information

Brand	RELOC
GTIN	00784231038659
Manufacturers Part Number	CE 120 F U 15 M5
UPC	784231038659

## Taxonomies, Classifications, and Categories

Category Description	CORD SETS [DRYER & RANGE CORDS & BOOSTER CABLES]
Type	Cable

## Packaging

Carton	1
Weight Per each	5

## Uses, Certifications, and Standards

Application	Education, Government, Offices & Banks, Retail
environmental conditions	Indoor
Mounting	Semi-recessed
standard	CSA, UL