

Eaton CE15DNS3AB

Catalog Number: CE15DNS3AB

Eaton XT IEC contactor, 18A, 110-120 Vac, 50-60 Hz, 1NO, 18A, Frame D, 55 mm, 50-60 Hz, 1 hp, Side, Three-pole, Non-reversing, No overload relay, Freedom, Contactor



General specifications

Product Name

Eaton XT IEC contactor

UPC

782113778785

Product Height

2.96 in

Product Weight

1.01 lb

Compliances

ISO 9000

DIN VDE 0600

Catalog Notes

No enclosure

Catalog Number

CE15DNS3AB

Product Length/Depth

3.25 in

Product Width

1.8 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

IEC Rated

CSA Certified

UL Listed

defaultTaxonomyAttributeLabel

Amperage Rating

18A

HP rating - max

1 hp

Number Of Poles

Three-pole

Type

Contactors

Frequency rating

50-60 Hz

Frame size

55 mm

Coil voltage

110-120 Vac, 50-60 Hz

Contact configuration

1 NO

Continuous ampere rating

18 A

Relay

No overload relay

Series

Freedom

Operation

Non-reversing

Mounting method

Side

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

[Motor Starters and Contactors — Low Voltage Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - CE15DNS3AB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)