

Eaton CE15FNS3AB

Catalog Number: CE15FNS3AB

Eaton Freedom series IEC contactor, F-frame, Non-reversing, No overload relay, 32A, Three-pole, 2 hp max, Steel mounting plate, 1NO Side mounted auxiliary contact, 110/120 VAC, 50/60 Hz



General specifications

Product Name

Eaton XT IEC contactor

Catalog Number

CE15FNS3AB

UPC

782113779263

Product Length/Depth

3.25 in

Product Height

2.96 in

Product Width

1.8 in

Product Weight

1.01 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

DIN VDE 0600
ISO 9000

Certifications

IEC Rated
CSA Certified
UL Listed

Catalog Notes

No enclosure

defaultTaxonomyAttributeLabel

Amperage Rating

32A

HP rating - max

2 hp

Number Of Poles

Three-pole

Type

Contactors

Frequency rating

50-60 Hz

Frame size

F

Coil voltage

110-120 Vac, 50/60 Hz

Contact configuration

1 NO

Relay

No overload relay

Series

Freedom

Operation

Non-reversing

Mounting method

Side

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

[Motor Starters and Contactors — Low Voltage Catalog](#)

Specifications and datasheets

[Eaton Specification Sheet - CE15FNS3AB](#)