

Floor Boxes

SystemOne ETERNAL™ Series Concrete Floorboxes

4-Gang Recessed

HUBBELL

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- PVC base construction for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Rectangular cover, patented labor saving easy mount device plates



Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Rectangular	On/ Above Grade	783585695433	CFB4G30PFBE

Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	PVC
Box Finish	Gray
Top Mounting Plates	16 gauge galvanized steel
Flush Prepour Cover	16 gauge galvanized steel
1/2" Prepour Cover	Yellow Plastic
Device Chamber Grounding	Green #10-32 Screw
Wiring Chamber Volumes	(4) 51.0 IN ³ [835 CM ³]

Performance

Mechanical

Depth of Pour, Minimum	3.25" (82.6)
Depth of Pour, Recommended	3.75" (95.3)
Floor Box Cover Series	24Gxx
Floor Box Height	3.17"[80.4mm]
Floor Box Length	15.70" [398.8mm]
Floor Box Width	11.20" [284.5mm]
PVC Conduit Entry: Bottom	Requires Drilling Openings. PVC Conduit Only: 1½" Maximum Size
PVC Conduit Entry: Ends	Requires Drilling Openings. PVC Conduit Only: 1¼" Maximum Size *

Related Products

(2) 2" PVC field installed hubs, ships with CFBHUB200PVC
(2) 1-1/2" reducer, (2) 1-1/4" reducers,
and (2) 1" reducers/plugs

(2) 1-1/4" PVC field installed hubs, ships CFBHUB125PVC
with (2) 1" reducers, (2) 3/4" reducers,
AND (2) 1/2" reducer/plugs

Rectangular pre-pour ½ in. extension 24GEXTENDCAP2PK
caps (2 pack)

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

