

Floor Boxes

SystemOne Recessed Floorboxes

4-Gang Recessed

Features

- 3.75" deep wiring chambers for large AV modules and feed-thru capacity
- External High Capacity Feed-Thru Hubs Sold Separately
- PVC base construction for on grade use, ships with Flush Installation Cover & 1/2" Prepour Cover
- Pre and post pour adjustment
- Round cover, patented labor saving easy mount device plates

Ordering Information

Cover Style	Box Type	UPC	Catalog Number
Round	On/ Above Grade	783585695440	CFB4G30PFBRE

Listings

cULus Listed
UL 514A Listed

Specifications

Box Material	PVC
Box Finish	Gray
Top Mounting Plates	16 gauge galvanized steel
Concrete Cover	16 gauge galvanized steel
Device Chamber Grounding	Green #10-32 Screw
Wiring Chamber Depth	3.75"
Wiring Chamber Volumes	(4) 51.0 IN ³ [835 CM ³]

Performance

Mechanical

Depth of Pour, Minimum	4.00 (101.6)
Depth of Pour, Recommended	4.00 (101.6)
Floor Box Cover Series	CFBS1R8xx
Floor Box Height	3.88"[98.6mm]
Floor Box Length	15.70" [398.8mm]
Floor Box Width	11.20" [284.5mm]
PVC Conduit Entry: Bottom	Requires Drilling Openings. PVC Conduit Only: 1½" Maximum Size
PVC Conduit Entry: Ends	Requires Drilling Openings. PVC Conduit Only: 1¼" Maximum Size *

HUBBELL



Related Products

(2) 2" PVC field installed hubs, ships with CFBHUB200PVC
(2) 1-1/2" reducer, (2) 1-1/4" reducers,
and (2) 1" reducers/plugs

(2) 1-1/4" PVC field installed hubs, ships CFBHUB125PVC
with (2) 1" reducers, (2) 3/4" reducers,
AND (2) 1/2" reducer/plugs

3/4" Prepour stackable ring extensions CFB8RCVRR075

Online Resources

Customer Sales Drawings
eCatalog
Installation Instructions

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

