

Eaton CFSR-2023-M15

Catalog Number: CFSR-2023-M15

Eaton Crouse-Hinds series PowerGard replacement receptacle, 20A, Two-wire, three-pole, Copper-free aluminum, Single-gang, M15 model, 125 Vac

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series PowerGard replacement receptacle	CFSR-2023-M15
	UPC 662276515529
Product Length/Depth	Product Height
5.25 in	6.5 in
Product Width	Product Weight
4.38 in	1.89 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class II, Division 1

Class III

NEMA Rating

3

3R

Product specifications

Number of gangs

Single-gang

Configuration

Two-wire, three-pole

Amperage Rating

20A

Voltage rating

125 Vac

Material

Copper-free aluminum

Type

M15 model

Resources

Brochures

[PowerGard Explosionproof NEMA Locking Receptacles brochure](#)

Catalogs

[PowerGard Explosionproof NEMA Locking Receptacles catalog page](#)

Certification reports

[PowerGard Explosionproof NEMA Locking Receptacles Canadian certification \(Receptacles with Plugs\)](#)

[PowerGard Explosionproof NEMA Locking Receptacles UL certification \(PowerGard Receptacles and Back Boxes Classified for use with Crouse-Hinds ENP Plugs\)](#)

[PowerGard Explosionproof NEMA Locking Receptacles UL certification \(PowerGard Receptacles and Back Boxes Classified for use with Appleton ECP Plugs and EFS Receptacles\)](#)

[PowerGard Explosionproof NEMA Locking Receptacles Canadian certification \(Receptacles with Plugs Interlocked with Switches\)](#)

Installation instructions

[IF 1663 - PowerGard Receptacles](#)

Specifications and datasheets

[Eaton Specification Sheet - CFSR-2023-M15](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)