# Eaton CG125 1150

# Catalog Number: CG125 1150

Eaton Crouse-Hinds series CG color-coded cord grip, Cable range min/max: 1.05-1.15", Orange, Straight, Steel, 1-1/4"

## General specifications



Eaton Crouse-Hinds series CG color-

coded cord grip

Catalog Number

CG125 1150

UPC

784564001122

Product Length/Depth

1.94 in

2.03 in

**Product Height** 

2.03 in

**Product Width** 

roduct width

**Product Weight** 

0.4 lb





### Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

**NEMA Rating** 

4

#### **Product specifications**

Connector type

Straight

Material

Steel

Trade size

1-1/4"

Color

Orange

Cable range (min/max)

1.05-1.15"

#### Resources

#### 3D CAD drawing package

Eaton Crouse-Hinds CG125 1150 3D drawing

#### Catalogs

Crouse-Hinds series CG Color-coded Cord Grips catalog page

#### Certification reports

CG Color-coded Cord Grips Canadian certification

CG Color-coded Cord Grips UL certification

#### Specifications and datasheets

Eaton Specification Sheet - CG125 1150



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia