



Cord Grip Male Straight, 3/4-inch NPT, 0.500-inch-0.625-inch

Features & Benefits

- Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.
- They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.
- They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain.
- Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007996517
Country Of Origin	Mexico	Material	Aluminum
Construction	Various Types of Pulling, Support and Strain Relief Grips	Application Sector	Industrial
Standard	UL/CSA Approval (consult factory)	Type	Cord Grip

Dimensions

Product Width US	0.625 in	Cable Diameter Range	0.500-0.625 in
------------------	----------	----------------------	----------------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Maximum Cable Range	0.56 in	Grip Angle	Straight
Grip Fitting	Male	Minimum Cable Range	0.625 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
NPT Thread Size	3/4 in	Mounting	Consult the Factory for Mounting Recommendations
