

Bridgeport Fittings Inc.


705 Lordship Blvd. Stratford, CT 06615

Phone: 203-377-5944 Fax: 203-381-3488

US Steel

Images





Dimension A in Inches: .150-.250
Dimension B in Inches: .687
Dimension C in Inches: 1.210
Dimension D in Inches: 1.220
Dimension E in Inches: 1-5/16
Dimension F in Inches: 13/16

Application

These watertight fittings are designed for both indoor and outdoor applications. All fittings can be used in chemical and treatment plants as well as for offshore applications. Straight connector for use with portable cord provides liquid tight and water tight protection. Typical applications include wiring of motors, transformers, advanced machinery, refrigeration, and tools.

Product Information

Material: Steel

Finish: Zinc Electro-Plate

Certifications & Codes:

NEMA Standard: FB-1

UL File Number: E11259, cULus

UL Standard: UL514B UNSPSC: 39121431

Catalog ID: CG771-250

UPC Number: 78174727711

Description: Connector, cord grips, straight, steel, k.o. size-

3/4", cord range .150-.250

Application: These watertight fittings are designed for both indoor and outdoor applications. All fittings can be used in chemical and treatment plants as well as for offshore applications. Straight connector for use with portable cord provides liquid tight and water tight protection. Typical applications include wiring of motors, transformers, advanced machinery, refrigeration, and tools.

Trade Size: 3/4"

Country of Manufacture: USA

Std Pkg Qty: 100

Unit Qty: 10