

Eaton CGB117

Catalog Number: CGB117

Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.375-0.437", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 1/2" NPT

General specifications



| | |
|---|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series CGB cable gland | CGB117 |
| | UPC |
| | 782274130408 |
| Product Length/Depth | Product Height |
| 1.63 in | 0.97 in |
| Product Width | Product Weight |
| 0.97 in | 0.15 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

4

Product specifications

Protection type

General purpose

Cable type

Non-armoured

Tray cable

Gland type

Non-armoured

Thread Size

1/2"

Thread type

NPT

Cable range (min/max)

0.375-0.437"

Material

Steel

Resources

Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

Installation instructions

[IF 513A - CG Fittings Installation](#)

[IF 1826 - CGB, CGD and CGE Connectors](#)

Specifications and datasheets

[Eaton Specification Sheet - CGB117](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)