

Eaton CGB197

Catalog Number: CGB197

Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.750-0.875", Non-armoured and tray cable, Non-armoured, Steel, General purpose, 1/2" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGB cable gland	CGB197
	UPC
	782274131603
Product Length/Depth	Product Height
2.38 in	1.66 in
Product Width	Product Weight
1.66 in	0.52 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

3R

4

Product specifications

Protection type

General purpose

Cable type

Tray cable

Non-armoured

Gland type

Non-armoured

Thread Size

1/2"

Thread type

NPT

Cable range (min/max)

0.750-0.875"

Material

Steel

Resources

Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

Installation instructions

[IF 1826 - CGB, CGD and CGE Connectors](#)

[IF 513A - CG Fittings Installation](#)

Specifications and datasheets

[Eaton Specification Sheet - CGB197](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)