

# Eaton CGB396 SA

Catalog Number: CGB396 SA

Eaton Crouse-Hinds series CGB cable gland, Cable range min/max: 0.625-0.750", Non-armoured and tray cable, Non-armoured, Aluminum, General purpose, 1" NPT

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series CGB cable gland	CGB396 SA
	UPC
	782274100845
<b>Product Length/Depth</b>	<b>Product Height</b>
2.38 in	1.66 in
<b>Product Width</b>	<b>Product Weight</b>
1.66 in	0.22 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

3R

4X

## Product specifications

### Protection type

General purpose

### Cable type

Tray cable

Non-armoured

### Gland type

Non-armoured

### Thread Size

1"

### Thread type

NPT

### Cable range (min/max)

0.625-0.750"

### Material

Aluminum

## Resources

### Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

### Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

### Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

### Installation instructions

[IF 1826 - CGB, CGD and CGE Connectors](#)

[IF 513A - CG Fittings Installation](#)

### Specifications and datasheets

[Eaton Specification Sheet - CGB396 SA](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)