

Eaton CGE192

Catalog Number: CGE192

Eaton Crouse-Hinds series CGE cable gland, Cable range min/max: 0.125-0.250", Non-armoured and tray cable, 90° angle, Non-armoured gland, Feraloy iron alloy, General purpose, 1/2" NPT

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series CGE cable gland	CGE192
	UPC
	782274141954
Product Length/Depth	Product Height
2.87 in	1.14 in
Product Width	Product Weight
1.14 in	0.3 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4

Product specifications

Protection type

General purpose

Cable type

Non-armoured

Tray cable

Gland type

Non-armoured

Connector type

90° angle

Thread Size

1/2"

Thread type

NPT

Cable range (min/max)

0.125-0.250"

Material

Feraloy iron alloy

Resources

Brochures

[Crouse-Hinds series Tray Cable Glands brochure](#)

Catalogs

[Crouse-Hinds series CGB, CGD, CGE and CGFP Non-armoured Glands catalog page](#)

Certification reports

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification](#)

[CGB, CGD, CGE and CGFP Non-armoured Glands UL certification \(Cover\)](#)

Installation instructions

[IF 1826 - CGB, CGD and CGE Connectors](#)

[IF 513A - CG Fittings Installation](#)

Specifications and datasheets

[Eaton Specification Sheet - CGE192](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)