

Eaton CH10GEN5050SN

Catalog Number: CH10GEN5050SN

Eaton CH transfer switch panel, Switched neutral manual transfer switch, 50A main, 50A emergency, 10 circuits, NEMA 1 enclosure, 12 kW, (6) single-pole 15A, (2) single-pole 20A, (1) two-pole 30A feeder breakers, Standard T phasing

General specifications



Product Name

Eaton CH transfer switch panel

UPC

786685268378

Product Height

14.3 in

Product Weight

24 lb

Certifications

UL 67

UL 1008

Catalog Number

CH10GEN5050SN

Product Length/Depth

16.8 in

Product Width

4.4 in

Warranty

15 year on loadcenter

Catalog Notes

Extend Warranty to 20 Years by Purchasing an Emergency Generator Panel with Surge Protection. Lifetime Warranty on Branch Breaker.

defaultTaxonomyAttributeLabel

Type

Switched neutral manual transfer switch

Number of circuits

10

Phasing

Standard T

Wattage

12 kW

Amperage Rating

50A main, 50A emergency

Enclosure

NEMA 1

Rating of feeders

(6) single-pole 15 A, (2) single-pole 20 A, (1) two-pole 30 A

Resources

Brochures

[Manual Emergency Power Solution Sales Aid](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH10GEN5050SN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)