

Eaton CH18L3125R

Catalog Number: CH18L3125R

Eaton CH main lug loadcenter,Cover included,Main lug only,125 A,C,Copper,NEMA 3R,Metallic,Overhead,CH,18 Circuits,18 Spaces,Four-wire,Three-phase,#1-4/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH18L3125R
UPC	Product Length/Depth
782113097541	21 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
24 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Furnished with hub closure plates.

defaultTaxonomyAttributeLabel

Special features

Cover included

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

18

Number of spaces

18

Phase

Three-phase

Wire size

#1-4/0 AWG

Box size

C

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

35 kAIC

Number of wires

4

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 3 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH18L3125R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)