

Eaton CH2100

Catalog Number: CH2100

Eaton CH Thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 100 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, 14AWG – 1/0AWG, u/AI, CH, Type CH Loadcenters

General specifications



Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CH2100
	UPC
	782113102375
Product Length/Depth	Product Height
3.5 in	3.25 in
Product Width	Product Weight
1.5 in	0.65 lb
Certifications	Catalog Notes
UL 489	Two-Pole 120/240V Common Trip Requires Two 3/4-Inch Spaces

defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker

Amperage Rating

100 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

#10-1/0 AWG Cu/Al

Number of poles

Two-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type CH Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH2100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia