



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH2100CS Type CH BRKR 100A/2 Pole 120/240V 10K Clamshell *Eaton Corp*

Catalog Number	CH2100CS
Manufacturer	Eaton Corp
Description	Eaton CH Thermal Magnetic Circuit Breaker, Type CH 3/4-Inch Standard Circuit Breaker Clamshell Pack, Clamshell Pack, 100 A, 10 Kaic, Two-Pole, 120/240V, CH, Common Breaker Trip, #10-1/0 Awg Cu/Al, Q30, CH, Type CH Loadcenters
Weight per unit	0.6200 (lbs/each)
Product Category	2P Special Application Plug-In

Features

amperage rating	100 A
dimensions	6.0000 IN X 4.0000 IN X 2.2500 IN
interrupt rating	10 kAIC
Poles	Two-pole
Trip Type	Common breaker trip
Voltage Rating	120/240 V

Descriptions

Description	TYPE CH BRKR 100A/2 POLE 120/240V 10K CLAMSHELL
extra long description	ETN CH2100CS CH Breaker 100A/2 Pole
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous
Long Description	Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker clamshell pack, Clamshell pack, 100 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, Q30, CH, Type CH Loadcenters
Product Type	CH Breaker 100A/2 Pole 120/240V 10K
Special Features	Clamshell pack

Manufacturer Information

Brand	Eaton
GTIN	00782116630776
Manufacturers Part Number	CH2100CS
UPC	782116630776



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.62

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional Energy
standard	UL 489