



CH2100CS Type CH BRKR 100A/2 Pole 120/240V 10K Clamshell

Eaton Corp

| | |
|------------------|---|
| Catalog Number | CH2100CS |
| Manufacturer | Eaton Corp |
| Description | Eaton CH Thermal Magnetic Circuit Breaker, Type CH 3/4-Inch Standard Circuit Breaker Clamshell Pack, Clamshell Pack, 100 A, 10 Kaic, Two-Pole, 120/240V, CH, Common Breaker Trip, #10-1/0 Awg Cu/AI, Q30, CH, Type CH Loadcenters |
| Weight per unit | 0.6200 (lbs/each) |
| Product Category | 2P Special Application Plug-In |

Features

| | |
|------------------|-----------------------------------|
| dimensions | 6.0000 IN X 4.0000 IN X 2.2500 IN |
| interrupt rating | 10 |
| Poles | 2 |
| Voltage Rating | 120/240 V |

Descriptions

| | |
|------------------------|---|
| Description | TYPE CH BRKR 100A/2 POLE 120/240V 10K CLAMSHELL |
| extra long description | ETN CH2100CS CH Breaker 100A/2 Pole |
| Features | Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous |
| Long Description | Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker clamshell pack, Clamshell pack, 100 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, #10-1/0 AWG Cu/AI, Q30, CH, Type CH Loadcenters |
| Product Type | CH Breaker 100A/2 Pole 120/240V 10K |
| Special Features | Clamshell pack |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00782116630776 |
| Manufacturers Part Number | CH2100CS |
| UPC | 782116630776 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Powerdefense Breakers |
| Type | Thermal magnetic circuit breakers |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.62 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Generation - Renewable Energy - Alternative EnergyOtherDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional Energy |
| standard | UL 489 |