

Eaton CH2100CS

Catalog Number: CH2100CS

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker clamshell pack, Clamshell pack, 100 A, 10 kAIC, Two-pole, 120/240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, Q30, CH, Type CH Loadcenters

General specifications



Product Name

Eaton CH thermal magnetic circuit breaker

Catalog Number

CH2100CS

UPC

782116630776

Product Length/Depth

6 in

Product Height

2.25 in

Product Width

4 in

Product Weight

0.62 lb

Warranty

Limited lifetime residential, 1 year commercial

Certifications

UL 489

Catalog Notes

Two-Pole 120/240V Common Trip
Requires Two 3/4-Inch Spaces

defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker clamshell pack

Special features

Clamshell pack

Amperage Rating

100 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

#10-1/0 AWG Cu/Al

Number of poles

Two-pole

Quantity

30

Resources

Brochures

[Type CH Circuit Breakers and Loadcenters](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH2100CS](#)