

Eaton CH2150

Catalog Number: CH2150

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 150 A, 10 kAIC, Four-pole, 120/240V, CH, Common breaker trip, #3/0 AWG Cu/Al, CH, Type CH Loadcenters



General specifications

Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CH2150
	UPC
	782113298795

Product Length/Depth	Product Height
4.5 in	3 in

Product Width	Product Weight
3 in	1 lb

Warranty	Certifications
Limited lifetime residential, 1 year commercial	UL 489

Catalog Notes
Requires four-pole spaces and is not suitable for use on Three-phase panels, not CSA certified

defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker

Amperage Rating

150 A

Voltage rating

120/240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

#3/0 AWG Cu/Al

Number of poles

Four-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - CH2150](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)