

Eaton CH215GFT

Catalog Number: CH215GFT

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, 15 A, 10 kAIC, Two-pole, 120/240 V, CH, Common, Plug-on, #14-4 AWG, Ground fault self test, GFI



General specifications

Product Name	Catalog Number
Eaton CH GFCI circuit breaker	CH215GFT
UPC	Product Length/Depth
786676025614	4.5 in
Product Height	Product Width
2 in	2.75 in
Product Weight	Warranty
0.7 lb	10 year
Certifications	Catalog Notes
UL 489	Meets Federal Spec Classification W-C375

Type

Ground fault circuit breaker

Special features

Ground Fault Self Test

Amperage Rating

15 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault self test

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Plug-on

Wire size

#14-4 AWG

Number of poles

Two-pole

Brochures[Loadcenters and Circuit Breakers](#)**Specifications and datasheets**[Eaton Specification Sheet - CH215GFT](#)