



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CH22N125C 22C 125A 1PH Convertible Loadcenter

Eaton Corp

Catalog Number	CH22N125C
Manufacturer	Eaton Corp
Description	Convertible Loadcenter, 22 Spaces, 22 Circuits, 125 A, 120/240 V, #10 to #1/0 Awg Wire Size, Metallic (Enclosure) Material, Copper Bus Material, 21 In Overall Length, 14.31 In Overall Width, 3.88 In Overall Height, 14 LB
Weight per unit	14.0 (lbs/each)
Product Category	Single Phase Convertible Load

Features

amperage rating	125 VDC
Box Size	C
cover	Ch8cf-combination, ch8cs-surface
Cover Type	Ch8cf-combination, ch8cs-surface
dimensions	53.3400centimetreX36.3474centimetreX98.5520millimetre
main circuit breaker	CH
number of spaces	77442
Number of Wires	Three-wire
Phase	1 W

Material, Color, and Finish

Enclosure Material	METALLIC
--------------------	----------

Dimensions and Weight

Size	C
------	---

Descriptions

Description	22C 125A 1PH CONVERTIBLE LOADCENTER
-------------	-------------------------------------

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113098494
UPC	782113098494

Taxonomies, Classifications, and Categories

Category Description	LOADCENTERS & COVERS
igcc	CR487E403MN1AAAAA
unspsc code	39121101

Packaging

Carton	1
Weight Per each	14



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Enclosure	NEMA 1
standard	UL 67; UL 50



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH22N125C

UPC:782113098494

Dimensions:

- **Height:** 3.88 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

Notes: Panel does not include main. Order main breaker/lug kit separately. Loadcenters are factory bonded for service entrance apps. Remove bonding strap for separate neutral & ground bars for sub-feed apps.

Warranties:

- Limited lifetime

Specifications:

- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Copper
- **Cover:** Ch8cf-combination, ch8cs-surface
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Top/bottom
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 22
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #10-1/0 AWG

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CH CONVERTIBLE, INDOOR NEMA 1, 120/240 VAC, 1 PHASE](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)



- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH22N125C](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.