# Eaton CH230GFT

## Catalog Number: CH230GFT

Eaton CH GFCI circuit breaker, Ground fault circuit breaker, 30 A, 10 kAIC, Two-pole, 120/240 V, CH, Common, Plug-on, #14-4 AWG, Ground fault self test, GFI

### General specifications



Eaton CH GFCI circuit breaker

UPC

786676025645

**Product Height** 

2 in

**Product Weight** 

0.7 lb

Certifications

UL 489

Catalog Number

CH230GFT

Product Length/Depth

4.5 in

Product Width

2.75 in

Warranty

10 year

Catalog Notes

Meets Federal Spec Classification W-

C375





#### default Taxonomy Attribute Label

Type

Ground fault circuit breaker

Special features

**Ground Fault Self Test** 

Amperage Rating

30 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault self test

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

CH

Connection

Plug-on

Wire size

#14-4 AWG

Number of poles

Two-pole

#### Resources

**Brochures** 

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - CH230GFT



Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



