

Eaton CH main breaker loadcenter

CH24B200R

UPC:782113097787

Dimensions:

- **Height:** 5.19 IN
- **Length:** 29.13 IN
- **Width:** 14.31 IN

Weight:15.5 LB

Notes:Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Cover included
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** E
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 24
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil
- **Feed Type:** Overhead
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH](#)

- [Type CH Circuit Breakers and Loadcenters](#)
- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH24B200R](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

Eaton CH main breaker loadcenter

CH24B200R

UPC:782113097787

Dimensions:

- **Height:** 5.19 IN
- **Length:** 29.13 IN
- **Width:** 14.31 IN

Weight:15.5 LB

Notes:Furnished with tub hub closure plates for rainproof hubs, refer to page 3-22. Loadcenter contains single insulated/bondable neutral.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Cover included
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** E
- **Bus Material:** Copper
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 25 kAIC
- **Main Circuit Breaker:** CSR
- **Number Of Circuits:** 24
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2/0 AWG-300 kcmil
- **Feed Type:** Overhead
- **Voltage Rating:** 120/240V

Supporting documents:

- [Dimensional Drawing - CH 3/4 LOADCENTER, CSR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH](#)

- [Type CH Circuit Breakers and Loadcenters](#)
- [Loadcenters and Circuit Breakers](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eaton Specification Sheet - CH24B200R](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data