

Eaton CH24L125C

Catalog Number: CH24L125C

CH 3/4-inch loadcenter, Standard, Main lug only, 125A, C, Copper, Ch8cf-combination, ch8cs-surface, NEMA 1, Metallic, Top/bottom, CH, 24, 24, Three-wire, Single-phase, #6-2/0 AWG

General specifications



Product Name

Eaton CH main lug loadcenter

UPC

782113097695

Product Height

3.88 in

Product Weight

15 lb

Certifications

UL 67

UL 50

Catalog Number

CH24L125C

Product Length/Depth

29.13 in

Product Width

14.31 in

Warranty

Limited lifetime

Catalog Notes

Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard.



Powering Business Worldwide

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

125 A

Bus material

Copper

Cover

Ch8cf-combination, ch8cs-surface

Feed type

Top/bottom

Main circuit breaker

CH

Number of circuits

24

Number of spaces

24

Phase

Single-phase

Wire size

#6-2/0 AWG

Box size

C

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 1 PHASE

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH24L125C



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)