



Powering Business Worldwide

pe.eaton.com

CH 3/4-inch loadcenter

CH24L3125C

UPC:782113097657

Dimensions:

- **Height:** 5.19 IN
- **Length:** 21 IN
- **Width:** 14.31 IN

Notes:Furnished with hub closure plates.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Standard
- **Type:** Main lug only
- **Amperage Rating:** 125A
- **Box Size:** C
- **Bus Material:** Copper
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Feed Type:** Overhead or underground
- **Main Circuit Breaker:** CH
- **Number Of Circuits:** 24
- **Number Of Wires:** Four-wire
- **Phase:** Three-phase
- **Wire Size:** #1-4/0 AWG

Supporting documents:

- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Type CH Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - CH24L3125C](#)
- [Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 3 PHASE](#)



Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.