

# Eaton CH24L3125C

Catalog Number: CH24L3125C

Eaton CH main lug loadcenter, Standard, Main lug only, 125 A, C, Copper, NEMA 1, Metallic, Top/bottom, CH, 24 Circuits, 24 Spaces, Four-wire, Three-phase, #1-4/0 AWG



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main lug loadcenter	CH24L3125C
<b>UPC</b>	<b>Product Length/Depth</b>
782113097657	21 in
<b>Product Height</b>	<b>Product Width</b>
5.19 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
14 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67 UL 50	Furnished with hub closure plates.

## defaultTaxonomyAttributeLabel

### Special features

Standard

### Type

Main lug only

### Amperage Rating

125 A

### Bus material

Copper

### Feed type

Top/bottom

### Main circuit breaker

CH

### Number of circuits

24

### Number of spaces

24

### Phase

Three-phase

### Wire size

#1-4/0 AWG

### Box size

C

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

35 kAIC

### Number of wires

4

## Resources

### Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, INDOOR NEMA 1, 120/240 VAC, 3 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH24L3125C



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)