



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2020 Farmerville Highway
71270-0000, LA Ruston
Phone: 318-251-9393
Fax: 318-255-1402



CH260GFT Type BR 5 Ma GFI BRKR 60A/2 Pole 120/240V 10K_Self *Eaton Corp*

Catalog Number	CH260GFT
Manufacturer	Eaton Corp
Description	Ground Fault Circuit Breaker, 60 A, Common Tripping Mechanism, Line and Load Lug Terminal, Plug-On, #14 to #4 Awg Wire Size, 2 In Overall Height, 4.5 In Overall Length, 2.75 In Overall Width, 0.7 LB
Weight per unit	0.8000 (lbs/each)
Product Category	In Circuit Breakers

Features

connection	Plug-on
dimensions	4.5000 IN X 2.7500 IN X 2.0000 IN
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE BR 5 MA GFI BRKR 60A/2 POLE 120/240V 10K_SELF
extra long description	ETN CH260GFT BR 5 MA GFI 60A/2 POLE
Special Features	Ground Fault Self Test

Manufacturer Information

GTIN	00786676025669
UPC	786676025669

Taxonomies, Classifications, and Categories

Category Description	Fault Sensing Breakers (AFCI/GFCI)
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	0.8

Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper Converged
standard	UL 489