

# Eaton CH2L125RSE2P

Catalog Number: CH2L125RSE2P

Eaton CH main lug loadcenters, Standard, Main lug only, 125A, N/a, Copper, NEMA 3R, Metallic, Overhead, CH, 2, Two-pole, 2, Three-wire, Single-phase, 120/240 V, #14-1/0 AWG



## General specifications

### Product Name

Eaton CH main lug loadcenter

### Catalog Number

CH2L125RSE2P

### UPC

786676008471

### Product Length/Depth

9.5 in

### Product Height

3.13 in

### Product Width

4.5 in

### Product Weight

7.18 lb

### Warranty

Limited lifetime

### Certifications

UL 50

UL 67

### Catalog Notes

Rainproof panels are finished with hub closure plates. For use as service entrance applications only.

Neutral/ground holes (6) #14-6 and (3) #14-2/0 wag cu/al.



Powering Business Worldwide

## defaultTaxonomyAttributeLabel

### Special features

Standard

### Type

Main lug only

### Amperage Rating

125 A

### Bus material

Copper

### Feed type

Overhead

### Main circuit breaker

CH

### Number of circuits

2

### Number Of Poles

Two-pole

### Number of spaces

2

### Phase

Single-phase

### Voltage rating

120/240 V

### Wire size

#1-4/0 AWG

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH2L125RSE2P



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)