Eaton CH2L40SP

Catalog Number: CH2L40SP

Eaton CH main lug loadcenters,Standard,Main lug only,40A,5,Copper,NEMA 1,Metallic,Top/bottom,CH,Surface,2,Four-pole,2,Three-wire,Singlephase,120/240 V,#14-6 AWG



General specifications

Product Name Eaton CH main lug loadcenter

UPC

782114190418

Product Height 4.1 in

Product Weight 13.3 lb

Certifications UL 67

UL 50

Catalog Number CH2L40SP

Product Length/Depth 22.2 in

Product Width 15.1 in

Warranty Limited lifetime

Catalog Notes

Ground bar kits priced separately. Suitable for use as service equipment when not more than two service disconnecting mains are provided or when not used as a lighting and appliance panelboard.



defaultTaxonomyAttributeLabel

Special features

Standard

Туре

Main lug only

Amperage Rating

40 A

Bus material

Copper

Feed type

Top/bottom

Main circuit breaker

СН

Mounting

Surface

Number of circuits

2

Number Of Poles

Four-pole

Number of spaces

2

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#14-6 AWG

Box size

5

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating 25 kAIC

Resources

BrochuresType CH Circuit Breakers and LoadcentersLoadcenters and Circuit BreakersCatalogsEaton's Volume 1—Residential and Light CommercialInstallation instructionsCutler-Hammer Type CH and BR Loadcenters - InstructionsMultimediaAFCI Educational VideoSpecifications and datasheetsEaton Specification Sheet - CH2L40SP

3



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Righ Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia