

# Eaton CH30B3200L

Catalog Number: CH30B3200L

Eaton CH main breaker loadcenter, Standard, Main breaker, 200 A, L, Copper, NEMA 1, Metallic, 10 kAIC, CC, 30 Circuits, 30 Spaces, Four-wire, Three-phase, #2/0 AWG-300 kcmil, Top/bottom



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CH30B3200L
<b>UPC</b>	<b>Product Length/Depth</b>
782113097961	39 in
<b>Product Height</b>	<b>Product Width</b>
3.88 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
26 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Furnished with hub closure plates.

## defaultTaxonomyAttributeLabel

### Special features

Standard

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Main circuit breaker

CC

### Number of circuits

30

### Number of spaces

30

### Phase

Three-phase

### Wire size

#2/0 AWG-300 kcmil

### Feed type

Top/bottom

### Box size

L

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

4

## Resources

### Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, CC MAIN BREAKER, INDOOR NEMA 1, 120/240 VAC, 3 PHASE

### Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH30B3200L



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)