

Eaton CH3100

Catalog Number: CH3100

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 100 A, 10 kAIC, Three-pole, 240V, CH, Common breaker trip, #10-1/0 AWG Cu/Al, CH, Type CH Loadcenters



General specifications

| | |
|---|--|
| Product Name | Catalog Number |
| Eaton CH thermal magnetic circuit breaker | CH3100 |
| | UPC |
| | 782113102405 |
| Product Length/Depth | Product Height |
| 2.2 in | 2.6 in |
| Product Width | Product Weight |
| 3.1 in | 0.85 lb |
| Certifications | Catalog Notes |
| UL 489 | Three-Pole 240V Common Trip Requires Three 3/4-Inch Spaces |

defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker

Amperage Rating

100 A

Voltage rating

240 V - 240 V

Trip Type

Common breaker trip

Circuit breaker type

CH

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

CH

Wire size

#10-1/0 AWG Cu/Al

Number of poles

Three-pole

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

[Type CH Circuit Breakers and Loadcenters](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH3100](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)