

Eaton CH32L225R

Catalog Number: CH32L225R

Eaton CH main lug loadcenters, Standard, Main lug only, 225A, D, Copper, NEMA 3R, Metallic, Overhead, CH, 32, 32, Three-wire, Single-phase, 120/240 V, #4 AWG-300 kcmil

General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CH32L225R
UPC	Product Length/Depth
782113098043	29.13 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
15.5 lb	Limited lifetime
Certifications	Catalog Notes
UL 67 UL 50	Rainproof panels are furnished with hub closure plates. Suitable for use as a service equipment when a circuit breaker is used as a main breaker. The main breaker is backfed and requires hold-down bracket kit catalog number ch125rb.



defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main lug only

Amperage Rating

225 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CH

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#4 AWG-300 kcmil

Box size

D

Enclosure

NEMA 3R

Enclosure material

Metallic

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - CH 3/4 LOADCENTER, MAIN LUG ONLY, OUTDOOR NEMA 3R, 120/240 VAC, 1 PH

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH32L225R



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)