

Eaton CH32NLPN225J

Catalog Number: CH32NLPN225J

Eaton CH 3/4-in Eaton CH loadcenter, single-phase, 32 circuits, 32-pole, #2-300 kcmil wire, 225A, NEMA 1



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CH32NLPN225J
UPC	Product Length/Depth
786685347493	36 in
Product Height	Product Width
5.5 in	15 in
Product Weight	Warranty
20 lb	Limited lifetime
Certifications	Catalog Notes
UL 67	Main lug only/convertible plug-on neutral
UL 50	loadcenters-with factory installed main
Contact Manufacturer	lugs

defaultTaxonomyAttributeLabel

Special features

Plug-on neutral

Type

Convertible loadcenter

Amperage Rating

225 A

Bus material

Copper

Cover

Ch8nljf-combination, ch8nljs-surface

Main circuit breaker

CH

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Box size

J

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Main lug wire size

#6-330 kcmil

Number of wires

3

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH32NLPN225J



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)