Eaton CH360ST

Catalog Number: CH360ST

Eaton CH thermal magnetic circuit breaker, Type CH 3/4-Inch standard circuit breaker, 60 A, 10 kAIC, Three-pole, 240V, CH, Common breaker trip, #10-1/0 AWG Cu/AI, CH, Type CH Loadcenters, Shunt trip included

General specifications



Product Name

Eaton CH thermal magnetic circuit breaker

Product Length/Depth

4.8 in

Product Width

3.5 in

Warranty

Limited lifetime residential, 1 year commercial

Catalog Number

CH360ST

UPC

782113328379

Product Height

3.5 in

Product Weight

1.15 lb

Certifications

UL 489

Catalog Notes

Three-Pole 240V Common Trip Requires

Three 3/4-Inch Spaces



defaultTaxonomyAttributeLabel

Type

Type CH 3/4-Inch standard circuit breaker

Special features

Shunt Trip

Amperage Rating

60 A

Voltage rating

240 V - 240 V

Trip Type

Common breaker trip

Circuit breaker type

СН

Shunt trip

Included

Used with

Type CH Loadcenters

Interrupt rating

10 kAIC

Main circuit breaker

СН

Wire size

#10-1/0 AWG Cu/AI

Number of poles

Three-pole

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Specifications and datasheets

Eaton Specification Sheet - CH360ST



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective









