

CH 3/4-inch Main Loadcenter

CH42B200V



General Description

CH 3/4-inch Main Loadcenter, single-phase, 42 circuits, #2-300 kcmil wire, 200A, NEMA 1 enclosure

Warranty

Limited lifetime

Product Specifications

Package: 4.25 x 39 x 15.75 in.

Package Weight: 41.18 lbs.

Product Dimensions: 3.88 x 37 x 14.31 in.

- Certification: UL 67, UL 50
- Amperage rating: 200A
- Enclosure: Metallic NEMA 1
- Interrupt Rating: 25 kAIC
- Main circuit breaker: CSR
- Three-wire
- Single-phase
- Wire size: #2-300 kcmil
- 42 circuits
- 42 spaces
- Box size: K
- Copper bus
- Value pack includes (5) CH120 and (1) CH230 breakers



Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2014 Eaton
All Rights Reserved
Printed in USA
August 2014

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.

CH 3/4-inch Main Loadcenter

CH42B200V



General Description

CH 3/4-inch Main Loadcenter, single-phase, 42 circuits, #2-300 kcmil wire, 200A, NEMA 1 enclosure

Warranty

Limited lifetime

Product Specifications

Package: 4.25 x 39 x 15.75 in.

Package Weight: 41.18 lbs.

Product Dimensions: 3.88 x 37 x 14.31 in.

- Certification: UL 67, UL 50
- Amperage rating: 200A
- Enclosure: Metallic NEMA 1
- Interrupt Rating: 25 kAIC
- Main circuit breaker: CSR
- Three-wire
- Single-phase
- Wire size: #2-300 kcmil
- 42 circuits
- 42 spaces
- Box size: K
- Copper bus
- Value pack includes (5) CH120 and (1) CH230 breakers



Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2014 Eaton
All Rights Reserved
Printed in USA
August 2014

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.