

Eaton CH42B200V

Catalog Number: CH42B200V

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 1, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH42B200V
UPC	Product Length/Depth
782114810880	37 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15.75 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Value packs breakers included 5-ch120 & 1-ch230

defaultTaxonomyAttributeLabel

Special features

Standard

Type

Main breaker

Amperage Rating

200 A

Bus material

Copper

Main circuit breaker

CSR

Number of circuits

42

Number of spaces

42

Phase

Single-phase

Wire size

#2 AWG-300 kcmil

Box size

K

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH42B200V](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)