

Eaton CH50SPAST

Catalog Number: CH50SPAST

Eaton CH 3/4 in Spa Panel, CH Spa panel-quick pro, 50 circuits, single-phase, three-wire, 50 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature



General specifications

| | |
|-----------------------|---|
| Product Name | Catalog Number |
| Eaton CH spa panel | CH50SPAST |
| UPC | Product Length/Depth |
| 786685969893 | 3.13 in |
| Product Height | Product Width |
| 4.5 in | 4.5 in |
| Product Weight | Warranty |
| 7.35 lb | Limited lifetime |
| Certifications | Catalog Notes |
| Contact Manufacturer | Includes a ch250gfi breaker, factory installed, and two extra circuits for convenience. Includes Ground fault self-test feature |

Type

Ch spa panel-quick pro

Amperage Rating

50A

Number of circuits

50

Number Of Poles

Two-pole

Phase

Single-phase

Used with

Ch spa panel

Wire size

#14-1/0 AWG Cu/Al

Box size

5R

Enclosure

NEMA 3R

Number of wires

3

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Specifications and datasheets

[Eaton Specification Sheet - CH50SPAST](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)