

Specifications



Photo is representative

Eaton CH60SPAST

Eaton CH 3/4 in spa panel, ch spa panel-quick pro, single-phase, three-wire, 60 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature

General specifications

PRODUCT NAME	Eaton CH spa panel
CATALOG NUMBER	CH60SPAST
UPC	786685969909
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	3.13 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	7.55 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	Contact Manufacturer
CATALOG NOTES	Includes a ch260gfi breaker, factory installed, and two extra circuits for convenience. Includes ground fault self-test feature.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Includes ch230gfi breaker GS ST
TYPE	Ch spa panel-quick pro
AMPERAGE RATING	60A
NUMBER OF POLES	Two-pole
PHASE	Single-phase
USED WITH	Ch spa panel
WIRE SIZE	#14-1/0 AWG Cu/Al
BOX SIZE	5R
ENCLOSURE	NEMA 3R
NUMBER OF WIRES	3
SIZE	3/4 in

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH60SPAST

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Photo is representative

Eaton CH60SPAST

Eaton CH 3/4 in spa panel, ch spa panel-quick pro, single-phase, three-wire, 60 A, #14-1/10 AWG at Cu/Al at 60/75° wire, ground fault self-test feature

General specifications

PRODUCT NAME	Eaton CH spa panel
CATALOG NUMBER	CH60SPAST
UPC	786685969909
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	3.13 in
PRODUCT WIDTH	1.5 in
PRODUCT WEIGHT	7.55 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	Contact Manufacturer
CATALOG NOTES	Includes a ch260gfi breaker, factory installed, and two extra circuits for convenience. Includes ground fault self-test feature.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Includes ch230gfi breaker GS ST
TYPE	Ch spa panel-quick pro
AMPERAGE RATING	60A
NUMBER OF POLES	Two-pole
PHASE	Single-phase
USED WITH	Ch spa panel
WIRE SIZE	#14-1/0 AWG Cu/Al
BOX SIZE	5R
ENCLOSURE	NEMA 3R
NUMBER OF WIRES	3
SIZE	3/4 in

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH60SPAST

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

