Eaton CH6L3125SP

Catalog Number: CH6L3125SP

Eaton CH main lug loadcenter, Main lug only, 125 A,7, Copper, Cover not included, NEMA 1, Metallic, Top/bottom, CH, #14-1/2 AWG, Surface, 6 Circuits, 6 Spaces, Four-wire, Three-phase, 120/240V, 208Y/120, 240V





Eaton CH main lug loadcenter

UPC

782114229231

Product Height

3.56 in

Product Weight

9.9 lb

Certifications

UL 67 UL 50 Catalog Number

CH6L3125SP

Product Length/Depth

13 in

Product Width

11 in

Warranty

Limited lifetime

Catalog Notes

Suitable for use as service equipment when not more than two service disconnecting means are provided or when not more than six service disconnecting means are provided and when not used as a lighting and appliance panelboard





defaultTaxonomyAttributeLabel Type Main lug only Amperage Rating 125 A Bus material Copper Cover Cover not included Feed type Top/bottom Main circuit breaker CH Mounting Surface Number of circuits 6

Number of spaces

6

Phase

Three-phase

Voltage rating

120/240V, 208Y/120, 240V

Box size

7

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

35 kAIC

Main lug wire size

#14-1/2 AWG

Number of wires

4

Resources

Brochures

Type CH Circuit Breakers and Loadcenters

Loadcenters and Circuit Breakers

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Installation instructions

Cutler-Hammer Type CH and BR Loadcenters - Instructions

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH6L3125SP



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia