

Eaton CH8BFM

Catalog Number: CH8BFM

Eaton Flush Mechanical Interlock Trim/Deadfront, Mechanical interlock -type a, Flush mechanical interlock trim/deadfront, B, NEMA 1, Flush, 0.75 in, CH12I125b, ch16I125b, ch12I3125b, ch14b100Ab



General specifications

Product Name	Catalog Number
Eaton CH cover	CH8BFM
UPC	Product Length/Depth
782113099590	17.8 in
Product Height	Product Width
1.1 in	14.3 in
Product Weight	Warranty
8.6 lb	Limited lifetime
Certifications	Catalog Notes
Contact Manufacturer	Interlocks two ch breakers mounted across from one another

Special features

Mechanical interlock -type a

Type

Cover

Amperage Rating

400 A

Bus material

Aluminum

Mounting

Flush

Phase

Three-phase

Used with

Ch12l125b, ch16l125b, ch12l3125b, ch14b100Ab

Box size

B

Enclosure

NEMA 1

Interrupt rating

10 kAIC

Size

3/4 in

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH8BFM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)