

Specifications



Eaton CH8KFM

Eaton Indoor Flush Mechanical Interlock Trim/Deadfront, Suitable for CH42NLPN225K, Indoor flush mechanical interlock trim/deadfront, Flush, 0.75 in, CH42b200k, ch42n200k, ch42b225k, CH42NLPN225K

General specifications

PRODUCT NAME	Eaton CH cover
CATALOG NUMBER	CH8KFM
UPC	782114799437
PRODUCT LENGTH/DEPTH	38 in
PRODUCT HEIGHT	1.1 in
PRODUCT WIDTH	15.3 in
PRODUCT WEIGHT	15 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer
CATALOG NOTES	Covers mechanically interlock a main type csr breaker with a type ch.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Suitable for CH42NLPN225K
TYPE	Cover
AMPERAGE RATING	400 A
BUS MATERIAL	Aluminum
MOUNTING	Flush
PHASE	Three-phase
USED WITH	Ch42b200k, ch42n200k, ch42b225k, CH42NLPN225K
ENCLOSURE	NEMA 1
INTERRUPT RATING	10 kAIC
SIZE	3/4 in

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH8KFM
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

Specifications



Eaton CH8KFM

Eaton Indoor Flush Mechanical Interlock Trim/Deadfront, Suitable for CH42NLPN225K, Indoor flush mechanical interlock trim/deadfront, Flush, 0.75 in, CH42b200k, ch42n200k, ch42b225k, CH42NLPN225K

General specifications

PRODUCT NAME	Eaton CH cover
CATALOG NUMBER	CH8KFM
UPC	782114799437
PRODUCT LENGTH/DEPTH	38 in
PRODUCT HEIGHT	1.1 in
PRODUCT WIDTH	15.3 in
PRODUCT WEIGHT	15 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer
CATALOG NOTES	Covers mechanically interlock a main type csr breaker with a type ch.



Powering Business Worldwide

Product specifications

SPECIAL FEATURES	Suitable for CH42NLPN225K
TYPE	Cover
AMPERAGE RATING	400 A
BUS MATERIAL	Aluminum
MOUNTING	Flush
PHASE	Three-phase
USED WITH	Ch42b200k, ch42n200k, ch42b225k, CH42NLPN225K
ENCLOSURE	NEMA 1
INTERRUPT RATING	10 kAIC
SIZE	3/4 in

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
MULTIMEDIA	AFCI Educational Video
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - CH8KFM
WARRANTY GUIDES	Eaton type CH circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.

