

Eaton CH8N200RF

Catalog Number: CH8N200RF

Eaton CH main breaker loadcenters, Convertible, 200 A, E, Copper, Not included, NEMA 3R, Metallic, 25 kAIC, CH, 8, Eight-pole, 8, Three-wire, Single-phase, #4 AWG-300 kcmil, Top/bottom, Flush, 120/240 V



General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH8N200RF
UPC	Product Length/Depth
782113098418	29.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15.75 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Furnished with hub closure plates. Includes feed-through lugs for both phase and neutral conductors.

defaultTaxonomyAttributeLabel

Type

Convertible

Amperage Rating

200 A

Bus material

Copper

Cover

Not included

Main circuit breaker

CH

Number of circuits

8

Number Of Poles

Eight-pole

Number of spaces

8

Phase

Single-phase

Wire size

#4 AWG-300 kcmil

Feed type

Top/bottom

Mounting

Flush

Voltage rating

120/240 V

Box size

E

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

[Type CH Circuit Breakers and Loadcenters](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 1—Residential and Light Commercial](#)

Installation instructions

[Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CH8N200RF](#)

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia