

Eaton CHB120

Catalog Number: CHB120

Eaton CH thermal magnetic circuit breaker, Ground fault circuit breaker, 5 mA Ground fault, 20 A, 10 kAIC, Single-pole, 120/240 V, #14-8 AWG, CHB, CH Loadcenters

General specifications



Product Name	Catalog Number
Eaton CH thermal magnetic circuit breaker	CHB120
	UPC
	782113112350
Product Length/Depth	Product Height
8.3 in	4.4 in
Product Width	Product Weight
4.5 in	0.2 lb
Warranty	Certifications
Limited lifetime	UL 489
	Contact Manufacturer

Type

Circuit breaker

Special features

5 mA Ground fault

Amperage Rating

20 A

Voltage rating

120/240 V

Circuit breaker type

CHB

Used with

CH Loadcenters

Interrupt rating

10 kAIC

Wire size

#14-8 AWG

Number of poles

Single-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 12—Aftermarket, Renewal Parts and Life Extension Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - CHB120](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia